22'4" X 40'2" MIRAGE

DIMENSIONS

40'1%"

4

PERIMETER

103'3"

Ħ

ARE/

21528 898

17!


3'4" 48

16'13/,"

ဖ œ

22'41/4'

20'7"



8

CO

ATTENTION DEALER/BUILDER:

INSTALLED IN NO DIVING AREAS

ADDITTIONAL NOTES

Rough excavation should be 2" to 3" deeper in each instance.

EXCAVATION NOTES

16'91/4"

20'3/4"

S4-A

15'81/4"

16'11"

23'6"

20'31/2"

- Dimensions are from inside pool panels.
 The water level should be no more than 6" below the coping receptor (hangtab) slot.

GENERAL NOTES

hese are finished dimensions ready for the liner

Document ID: HF5100, Hydra Standard Panel Layout Drawing Rev Date: 1216/2005 Rev Level: A

- Sol to have minimum bearing capacity of 2000 P.S.F.
 Locate top of pool at least 6" above surrounding land elevation.
 Locate top of pool at least 6" above surround pool.
 Sel Panel Shelf Detail for excavation around pool.
 Hill voids under base of panels and tamp well.
 Backfill with non-expansive material.
 - THIS DOCUMENT IS FOR ILLUSTRATIVE PURPOSES ONLY.

only to normal ground conditions. There may be additional precautions and/or methods of agent of the Manufacturer. The construction methods Illustrated here are suggestions and apply The dealer or contractor who sells or installs your pool is an independant contractor and is not an Proper installation is the responsibility of the dealer/builder/contractor.


JAN 2006


HYDRA

22'4" X 40'2" MIRAGE

| NO DIVING WARNING | AYOUT | PING LAYOUT |
|--|-----------------------------|-------------|
| WHERE WEEDED ADVINOM PERIMETER OF BOND BEAM PERIMETER OF BOND BEAM | | |
| | | |
| 6" 10 8" DEEP | BRACE | HP199 |
| CONCRETE BOND BEAM | HP119M 9'R REVERSE | HP119M |
| EARTH TO SAND BOTTOM | HP115 (9'R) 1' OVAL INSERT | HP115 |
| | HP110 (9'R) 2' OVAL INSERT | HP110 |
| BACKFILL 0 | HP125 (9'R) 3' ROMAN INSERT | HP125 |
| USE NON-EXPANSIVE | HP159A 9'R PANEL (A/G) | HP159A |
| OV VINYL LINER | HP159LL 9'R PANEL (LIGHT) | HP159LL |
| BRACE | HP159 9'R PANEL | HP159 |
| POLYMER | HP116 1'8" SPECIAL PANEL | HP116 |
| | HP102 2' PANEL | HP102 |
| | HP103 3' PANEL | HP103 |
| APPROX 4" DEEP —————————————————————————————————— | HP106A 6' PANEL (A/G) | HP106A |
| | DESCRIPTION | PART |
| PANEL SHELF DETAIL | LL OF MATERIALS | L OF M |
| | U - | 4' |

ವ





191





10915